

## Non-Tilt Automatic Overbed Table H

HCPCS:



- Spring loaded lift mechanism positions top in 1" increments from 30" 45"
- ¾" x 15" x 30" high pressure laminate top with T- molding
- 1.5" Casters
- 100 lbs weight capacity
- Available with "H" base in chrome or opal powder coat
- Optional dual mirror vanity drawer
- Base and columns available in additional powder coat finishes
- Available on drop ship basis only

| PRODUCTS    | Description                      |
|-------------|----------------------------------|
| 16010-HCBO  | OBT-Auto-BO-H-Chrm-SpclOrdr      |
| 16010-HCBOV | OBT-Auto-BO-H-Chrm-Van-SpclOrdr  |
| 16010-HCDM  | OBT-Auto-DM-H-Chrm-SpclOrdr      |
| 16010-HCDMV | OBT-Auto-DM-H-Chrm-Van-SpclOrdr  |
| 16010-HCEO  | OBT-Auto-EO-H-Chrm-SpclOrdr      |
| 16010-HCEOV | OBT-Auto-EO-H-Chrm-Van-SpclOrdr  |
| 16010-HCFM  | OBT-Auto-FM-H-Chrm-SpclOrdr      |
| 16010-HCFMV | OBT-Auto-FM-H-Chrm-Van-SpclOrdr  |
| 16010-HCGW  | OBT-Auto-GW-H-Chrm               |
| 16010-HCGWV | OBT-Auto-GW-H-Chrm-Van-SpclOrdr  |
| 16010-HCNT  | OBT-Auto-NT-H-Chrm-SpclOrdr      |
| 16010-HCNTV | OBT-Auto-NT-H-Chrm-Van-SpclOrdr  |
| 16010-HCQO  | OBT-Auto-QO-H-Chrm-SpclOrdr      |
| 16010-HCQOV | OBT-Auto-QO-H-Chrm-Van-SpclOrdr  |
| 16010-HCSO  | OBT-Auto-SO-H-Chrm-SpclOrder     |
| 16010-HCSOV | OBT-Auto-SO-H-Chrm-Van-SpclOrder |
| 16010-HCWC  | OBT-Auto-WC-H-Chrm-SpclOrdr      |
| 16010-HCWCV | OBT-Auto-WC-H-Chrm-Van-SpclOrdr  |
| 16010-HOBO  | OBT-Auto-BO-H-Opal-SpclOrdr      |
| 16010-HOBOV | OBT-Auto-BO-H-Opal-Van-SpclOrdr  |
| 16010-HODM  | OBT-Auto-DM-H-Opal-SpclOrdr      |
| 16010-HODMV | OBT-Auto-DM-H-Opal-Van-SpclOrdr  |
| 16010-HOEO  | OBT-Auto-EO-H-Opal-SpclOrdr      |
| 16010-HOEOV | OBT-Auto-EO-H-Opal-Van-SpclOrdr  |
| 16010-HOFM  | OBT-Auto-FM-H-Opal-SpclOrdr      |

## PRODUCTS

## Description

|             |                                  |
|-------------|----------------------------------|
| 16010-HOFMV | OBT-Auto-FM-H-Opal-Van-SpclOrdr  |
| 16010-HOGW  | OBT-Auto-GW-H-Opal-SpclOrdr      |
| 16010-HOGWV | OBT-Auto-GW-H-Opal-Van-SpclOrdr  |
| 16010-HONT  | OBT-Auto-NT-H-Opal-SpclOrdr      |
| 16010-HONTV | OBT-Auto-NT-H-Opal-Van-SpclOrdr  |
| 16010-HOQO  | OBT-Auto-QO-H-Opal-SpclOrdr      |
| 16010-HOQOV | OBT-Auto-QO-H-Opal-Van-SpclOrdr  |
| 16010-HOSO  | OBT-Auto-SO-H-Opal-SpclOrder     |
| 16010-HOSOV | OBT-Auto-SO-H-Opal-Van-SpclOrder |
| 16010-HOWC  | OBT-Auto-WC-H-Opal-SpclOrdr      |
| 16010-HOWCV | OBT-Auto-WC-H-Opal-Van-SpclOrdr  |