

Non-Tilt Automatic Overbed Table H

HCPCS:



- Spring loaded lift mechanism positions top in 1" increments from 30" 45"
- ¾" x 15" x 30" high pressure laminate top with T- molding
- 1.5" Casters
- 100 lbs weight capacity
- Available with "H" base in chrome or opal powder coat
- Optional dual mirror vanity drawer
- Base and columns available in additional powder coat finishes
- Available on drop ship basis only

PRODUCTS	Description
16010-HCBO	OBT-Auto-BO-H-Chrm-SpclOrdr
16010-HCBOV	OBT-Auto-BO-H-Chrm-Van-SpclOrdr
16010-HCDM	OBT-Auto-DM-H-Chrm-SpclOrdr
16010-HCDMV	OBT-Auto-DM-H-Chrm-Van-SpclOrdr
16010-HCEO	OBT-Auto-EO-H-Chrm-SpclOrdr
16010-HCEOV	OBT-Auto-EO-H-Chrm-Van-SpclOrdr
16010-HCFM	OBT-Auto-FM-H-Chrm-SpclOrdr
16010-HCFMV	OBT-Auto-FM-H-Chrm-Van-SpclOrdr
16010-HCGW	OBT-Auto-GW-H-Chrm
16010-HCGWV	OBT-Auto-GW-H-Chrm-Van-SpclOrdr
16010-HCNT	OBT-Auto-NT-H-Chrm-SpclOrdr
16010-HCNTV	OBT-Auto-NT-H-Chrm-Van-SpclOrdr
16010-HCQO	OBT-Auto-QO-H-Chrm-SpclOrdr
16010-HCQOV	OBT-Auto-QO-H-Chrm-Van-SpclOrdr
16010-HCSO	OBT-Auto-SO-H-Chrm-SpclOrder
16010-HCSOV	OBT-Auto-SO-H-Chrm-Van-SpclOrder
16010-HCWC	OBT-Auto-WC-H-Chrm-SpclOrdr
16010-HCWCV	OBT-Auto-WC-H-Chrm-Van-SpclOrdr
16010-HOBO	OBT-Auto-BO-H-Opal-SpclOrdr
16010-HOBOV	OBT-Auto-BO-H-Opal-Van-SpclOrdr
16010-HODM	OBT-Auto-DM-H-Opal-SpclOrdr
16010-HODMV	OBT-Auto-DM-H-Opal-Van-SpclOrdr
16010-HOEO	OBT-Auto-EO-H-Opal-SpclOrdr
16010-HOEOV	OBT-Auto-EO-H-Opal-Van-SpclOrdr
16010-HOFM	OBT-Auto-FM-H-Opal-SpclOrdr

PRODUCTS	Description
16010-HOFMV	OBT-Auto-FM-H-Opal-Van-SpclOrdr
16010-HOGW	OBT-Auto-GW-H-Opal-SpclOrdr
16010-HOGWV	OBT-Auto-GW-H-Opal-Van-SpclOrdr
16010-HONT	OBT-Auto-NT-H-Opal-SpclOrdr
16010-HONTV	OBT-Auto-NT-H-Opal-Van-SpclOrdr
16010-HOQO	OBT-Auto-QO-H-Opal-SpclOrdr
16010-HOQOV	OBT-Auto-QO-H-Opal-Van-SpclOrdr
16010-HOSO	OBT-Auto-SO-H-Opal-SpclOrder
16010-HOSOV	OBT-Auto-SO-H-Opal-Van-SpclOrder
16010-HOWC	OBT-Auto-WC-H-Opal-SpclOrdr
16010-HOWCV	OBT-Auto-WC-H-Opal-Van-SpclOrdr