

## Non-Tilt Automatic Overbed Table U

HCPCS:



- Spring loaded lift mechanism height adjustment from 30" 45"
- ¾" x 18" x 32" high pressure laminate top with T- molding
- 2" casters for easy maneuvering
- Column can be mounted on left or right side
- Optional dual mirror vanity drawer
- Available with "H" (Figure A) or "U" base in chrome or opal powder coat
- Base and columns available in additional powder coat finishes
- Available on drop ship basis only

| PRODUCTS    | Description                      |
|-------------|----------------------------------|
| 16009-UCBO  | OBT-Auto-LrgTp-BO-U-Ch-SpOr      |
| 16009-UCBOV | OBT-Auto-LrgTp-BO-U-Ch-Van-SpOr  |
| 16009-UCDM  | OBT-Auto-LrgTp-DM-U-Ch-SpOr      |
| 16009-UCDMV | OBT-Auto-LrgTp-DM-U-Ch-Van-SpOr  |
| 16009-UCEO  | OBT-Auto-LrgTp-EO-U-Ch-SpOr      |
| 16009-UCEOV | OBT-Auto-LrgTp-EO-U-Ch-Van-SpOr  |
| 16009-UCFM  | OBT-Auto-LrgTp-FM-U-Ch-SpOr      |
| 16009-UCFMV | OBT-Auto-LrgTp-FM-U-Ch-Van-SpOr  |
| 16009-UCGW  | OBT-Auto-LrgTp-GW-U-Ch-SpOr      |
| 16009-UCGWV | OBT-Auto-LrgTp-GW-U-Ch-Van-SpOr  |
| 16009-UCNT  | OBT-Auto-LrgTp-NT-U-Ch-SpOr      |
| 16009-UCNTV | OBT-Auto-LrgTp-NT-U-Ch-Van-SpOr  |
| 16009-UCQO  | OBT-Auto-LrgTpl-QO-U-Ch-SpOr     |
| 16009-UCQOV | OBT-Auto-LrgTpl-QO-U-Ch-Van-SpOr |
| 16009-UCSO  | OBT-Auto-LrgTp-SO-U-Ch-SpOr      |
| 16009-UCSOV | OBT-Auto-LrgTp-SO-U-Ch-Van-SpOr  |
| 16009-UCWC  | OBT-Auto-LrgTp-WC-U-Ch-SpOr      |
| 16009-UCWCV | OBT-Auto-LrgTp-WC-U-Ch-Van-SpOr  |
| 16009-UOBO  | OBT-Auto-LrgTp-BO-U-Op-SpOr      |
| 16009-UOBOV | OBT-Auto-LrgTp-BO-U-Op-Van-SpOr  |
| 16009-UODM  | OBT-Auto-LrgTp-DM-U-Op-SpOr      |
| 16009-UODMV | OBT-Auto-LrgTp-DM-U-Op-Van-SpOr  |
| 16009-UOEO  | OBT-Auto-LrgTp-EO-U-Op-SpOr      |
| 16009-UOEOV | OBT-Auto-LrgTp-EO-U-Op-Van-SpOr  |
| 16009-UOFM  | OBT-Auto-LrgTp-FM-U-Op-SpOr      |

## PRODUCTS

## Description

|             |                                  |
|-------------|----------------------------------|
| 16009-UOFMV | OBT-Auto-LrgTp-FM-U-Op-Van-SpOr  |
| 16009-UOGW  | OBT-Auto-LrgTp-GW-U-Op-SpOr      |
| 16009-UOGWV | OBT-Auto-LrgTp-GW-U-Op-Van-SpOr  |
| 16009-UONT  | OBT-Auto-LrgTp-NT-U-Op-SpOr      |
| 16009-UONTV | OBT-Auto-LrgTp-NT-U-Op-Van-SpOr  |
| 16009-UOQO  | OBT-Auto-LrgTpl-QO-U-Op-SpOr     |
| 16009-UOQOV | OBT-Auto-LrgTpl-QO-U-Op-Van-SpOr |
| 16009-UOSO  | OBT-Auto-LrgTp-SO-U-Op-SpOr      |
| 16009-UOSOV | OBT-Auto-LrgTp-SO-U-Op-Van-SpOr  |
| 16009-UOWC  | OBT-Auto-LrgTp-WC-U-Op-SpOr      |
| 16009-UOWCV | OBT-Auto-LrgTp-WC-U-Op-Van-SpOr  |