

Non-Tilt Pneumatic Cylinder Overbed Table U

HCPCS:



- Pneumatic cylinder lift mechanism infinite height adjustment from 27"42"
- ¾" x 18" x 32" high pressure laminate top with T- molding
- 2" casters for easy maneuvering
- Column can be mounted on left or right side
- Optional dual mirror vanity drawer
- Available with "H" (Figure A) or "U" base in Chrome or Opal powder coat
- Base and columns available in additional powder coat finishes
- Available on drop ship basis only

PRODUCTS	Description
16008-UCBO	OBT-PnmCyl-BO-U-Ch-SpclOrdr
16008-UCBOV	OBT-PnmCyl-BO-U-Ch-Van-SpclOrdr
16008-UCDM	OBT-PnmCyl-FM-U-Ch-SpclOrdr
16008-UCDMV	OBT-PnmCyl-FM-U-Ch-Van-SpclOrdr
16008-UCEO	OBT-PnmCyl-EO-U-Ch-SpclOrdr
16008-UCEOV	OBT-PnmCyl-EO-U-Ch-Van-SpclOrdr
16008-UCFM	OBT-PnmCyl-FM-U-Ch-SpclOrdr
16008-UCFMV	OBT-PnmCyl-FM-U-Ch-Van-SpclOrdr
16008-UCGW	OBT-PnmCyl-GW-U-Ch-SpclOrdr
16008-UCGWV	OBT-PnmCyl-GW-U-Ch-Van-SpclOrdr
16008-UCNT	OBT-PnmCyl-NT-U-Ch-SpclOrdr
16008-UCNTV	OBT-PnmCyl-NT-U-Ch-Van-SpclOrdr
16008-UCQO	OBT-PnmCyl-QO-U-Ch-SpclOrdr
16008-UCQOV	OBT-PnmCyl-QO-U-Ch-Van-SpclOrdr
16008-UCSO	OBT-PnmCyl-SO-U-Ch-SpclOrdr
16008-UCSOV	OBT-PnmCyl-SO-U-Ch-Van-SpclOrdr
16008-UCWC	OBT-PnmCyl-WC-U-Ch-SpclOrdr
16008-UCWCV	OBT-PnmCyl-WC-U-Ch-Van-SpclOrdr
16008-UOBO	OBT-PnmCyl-BO-U-Op-SpclOrdr
16008-UOBOV	OBT-PnmCyl-BO-U-Op-Van-SpclOrdr
16008-UODM	OBT-PnmCyl-FM-U-Op-SpclOrdr
16008-UODMV	OBT-PnmCyl-FM-U-Op-Van-SpclOrdr
16008-UOEO	OBT-PnmCyl-EO-U-Op-SpclOrdr
16008-UOEOV	OBT-PnmCyl-EO-U-Op-Van-SpclOrdr
16008-UOFM	OBT-PnmCyl-FM-U-Op-SpclOrd

PRODUCTS	Description
16008-U0FMV	OBT-PnmCyl-FM-U-Op-Van-SpclOrd
16008-U0GW	OBT-PnmCyl-GW-U-Opal
16008-U0GWV	OBT-PnmCyl-GW-U-Opal-Van
16008-U0NT	OBT-PnmCyl-NT-U-Op-SpclOrdr
16008-U0NTV	OBT-PnmCyl-NT-U-Op-Van-SpclOrdr
16008-U0QO	OBT-PnmCyl-QO-U-Op-SpclOrdr
16008-U0QOV	OBT-PnmCyl-QO-U-Op-Van-SpclOrdr
16008-U0SO	OBT-PnmCyl-SO-U-Op-SpclOrder
16008-U0SOV	OBT-PnmCyl-SO-U-Op-Van-SpclOrder
16008-U0WC	OBT-PnmCyl-WC-U-Op-SpclOrdr
16008-U0WCV	OBT-PnmCyl-WC-U-Op-Van-SpclOrdr