


Viper Plus GT Wheelchair with Universal Armrests

HCPCS:



- The new Viper Plus GT with Universal Armrests allows the user to easily convert the armrests into desk arm, half arm, and full arm with the push of a button. The armrests also adjust to eight individual heights in ½ increments for complete customization.
- Adjustable height and length, flip-back, removable, padded arms
- Built-in seat rail extensions and extendable upholstery easily adjusts seat depth from 16" to 18"
- All-Aluminum frame
- Dual Axle allows for multiple seat-to-floor height positions
- Over-center cross brace eliminates need for seat guides Works with seating and positioning accessories
- Adjustable angle back easily adjusts from 5° - 20°
- Adjustable height back adjusts from 17" - 19" in 1" increments, adaptable for individual patient needs
- Durable, heavy-gauge flame-retardant nylon upholstery with hook and loop fastener flaps
- Quick release, 24" composite Mag-style wheels are lightweight and maintenance free
- Adjustable angle caster forks have three height adjustments and angle adjustability
- Tool-free adjustable swing-away footrests also feature easy-to-access release handles
- Urethane rear tires and casters offer superior performance, smoother ride and are lightweight
- Adjustable anti-tipper with flip-up wheels Never needs to be removed
- Comes with push-to-lock wheel locks

| PRODUCTS | Description |
|-------------------|-------------------------------------|
| PLA416FBUARAD-ELR | ViperPlsGT,16"FlpBk.UniArm,ELR,1/ea |
| PLA416FBUARAD-SF | ViperPlsGT,16"FlpBk.UniArm,SF,1/ea |
| PLA418FBUARAD-ELR | ViperPlsGT,18"FlpBk.UniArm,ELR,1/ea |
| PLA418FBUARAD-SF | ViperPlsGT,18"FlpBk.UniArm,SF,1/ea |
| PLA420FBUARAD-ELR | ViperPlsGT,20"FlpBk.UniArm,ELR,1/ea |
| PLA420FBUARAD-SF | ViperPlsGT,20"FlpBk.UniArm,SF,1/ea |
| PLA422FBUARAD-ELR | ViperPlsGT,22"FlpBk.UniArm,ELR,1/ea |
| PLA422FBUARAD-SF | ViperPlsGT,22"FlpBk.UniArm,SF,1/ea |

| SPECIFICATIONS | Description |
|----------------------|---|
| Warranty | Limited Lifetime |
| Product Weight | 34.5 lb |
| Product Dimensions | 46" (L) w/ riggings x 24" (W) x 36.3" (H) |
| Material | Aluminum |
| Seat Dimensions | 18" (W) x 16" - 18" (D) |
| Weight Capacity | 18" and 20": 300 lbs 22": 350 lbs |
| Seat To Floor Height | 17.5" - 19.5" |

| SPECIFICATIONS | Description |
|-------------------|--|
| Brakes | Push to lock |
| Anti-Tip Wheels | 2" |
| Arm Height | 12" -15.5" from seat |
| Back Angle Range | 0° - 20° |
| Color | Deep Green |
| Folded Dimensions | 33"x12.25"x36" |
| Back Height | 17" 18" 19" |
| ACCESSORIES | Description |
| STDS850 | Seat Belt, Clasp Type,1/ea, EA |
| STDS851 | Seat Belt, Velcro Close,1/ea, EA |
| STDS801GT | WheelLockExtension,ViperGT,SSP2,1/ea, EA |
| WASR | Limb Support, Right,1/cs, CS |
| WASL | Limb Support,Left,1/cs, CS |
| STDS840 | RearWheel,TreadedUrethane, Viper GT 1/ea, EA |
| STDS1034 | Wheelchair Cane/Crutch Holder,1/ea, EA |
| STDS828GT | AmputeeAdaptersViperGT,1pr, PR |
| STDS4056 | One Arm drive for ViperGT, EA |
| STDS860 | Forwrd Stablzrs/Univ.Fit ,1pr/bx, BX |
| STDS820 | Telescoping IV Pole,W/C, 1/bx, BX |
| STDS834 | OverheadAnti-Theft Bar,Single,1/ea, EA |
| STDSSHK | Super Hemi Kit Viper / Viper GT, 1kit/cs, CS |
| STDS807 | Anti-Tips,Adj.w/Whls,Blk,1pr/bx,10/cv, BX |