

Non-Tilt Designer Overbed Table H

HCPCS:



- Spring loaded lift mechanism provides infinite adjustment from 28" - 45"
- MDF core with formed vinyl top
- 1.5" x 30" top with ½" bullnose edgemold provides
- a protective ¼" lip against spills
- Twin wheel 2" casters for easy maneuvering
- Available with "H" or "U" base (Figure A) in Chrome or Opal Powder Coat
- Optional dual mirror vanity drawer
- Available on drop ship basis only

| PRODUCTS | Description |
|-------------|---------------------------------|
| 16011-HCFM | OBT-Designer-FM-H-Chrm-SpclOrdr |
| 16011-HCFMV | OBT-Designer-FM-H-Chrm-Van-Spcl |
| 16011-HCGN | OBT-Designer-GN-H-Chrm-SpclOrdr |
| 16011-HCGW | OBT-Designer-GW-H-Chrm-SpclOrdr |
| 16011-HCGWV | OBT-Designer-GW-H-Chrm-Van-Spcl |
| 16011-HCHM | OBT-Designer-HM-H-Chrm-SpclOrdr |
| 16011-HCQO | OBT-Designer-QO-H-Chrm-SpclOrdr |
| 16011-HCQOV | OBT-Designer-QO-H-Chrm-Van-Spcl |
| 16011-HCWC | OBT-Designer-WC-H-Chrm-SpclOrdr |
| 16011-HCWCV | OBT-Designer-WC-H-Chrm-Van-Spcl |
| 16011-HOFM | OBT-Designer-FM-H-Opal-Spcl |
| 16011-HOFMV | OBT-Designer-FM-H-Opal-Van-Spcl |
| 16011-HOGW | OBT-Designer-GW-H-Opal |
| 16011-HOGWV | OBT-Designer-GW-H-Opal-Van |
| 16011-HOQO | OBT-Designer-QO-H-Opal-Spcl |
| 16011-HOQOV | OBT-Designer-QO-H-Opal-Van-Spcl |
| 16011-HOWC | OBT-Designer-WC-H-Opal-Spcl |
| 16011-HOWCV | OBT-Designer-WC-H-Opal-Van-Spcl |

| SPECIFICATIONS | Description |
|------------------------|------------------|
| Warranty | Limited Lifetime |
| Height | 28" - 45" |
| Base Dimensions | 15" x 28" |
| Carton Shipping Weight | 28 lb |
| Weight | 25 lb |