

## Cruiser III Wheelchair

HCPCS: K0003,K0003



- Built-in seat rail extensions and extendable upholstery easily adjust seat depth from 16" to 18"
- Weighs under 36 lb (excluding front riggings)
- Carbon steel frame with silver vein finish
- Removable flip-back arms allow for easy transfer
- Frame style eliminates seat guides and allows for custom back inserts and accessories
- Nylon upholstery is durable, lightweight, attractive and easy-to-clean
- Composite, Mag-style wheels are lightweight and maintenance free
- Dual axle provides easy transition of seat height to hemi-level
- 8" front casters are adjustable in three positions
- Padded armrests provide additional comfort
- Comes with swing-away footrests or elevating leg rests with tool-free adjustable length riggings
- Precision sealed wheel bearings in front and rear ensure long-lasting performance and reliability
- Comes with push-to-lock wheel locks

| PRODUCTS     | Description                            |
|--------------|----------------------------------------|
| K316ADDA-ELR | Cruiser III, 16", Ht. Adj. FB DDA, ELR |
| K316ADDA-SF  | Cruiser III, 16", Ht. Adj. FB DDA, SF  |
| K316ADFA-ELR | Cruiser III, 16", Ht. Adj. FB DFA, ELR |
| K316ADFA-SF  | Cruiser III, 16", Ht. Adj. FB DFA, SF  |
| K316DDA-ELR  | Cruiser III, 16", FB DDA, ELR          |
| K316DDA-SF   | Cruiser III, 16", FB DDA, SF           |
| K316DFA-ELR  | Cruiser III, 16", FB DFA, ELR          |
| K316DFA-SF   | Cruiser III, 16", FB DFA, SF           |
| K318ADDA-ELR | Cruiser III, 18", Ht. Adj. FB DDA, ELR |
| K318ADDA-SF  | Cruiser III, 18", Ht. Adj. FB DDA, SF  |
| K318ADFA-ELR | Cruiser III, 18", Ht. Adj. FB DFA, ELR |
| K318ADFA-SF  | Cruiser III, 18", Ht. Adj. FB DFA, SF  |
| K318DDA-ELR  | Cruiser III, 18", FB DDA, ELR          |
| K318DDA-SF   | Cruiser III, 18", FB DDA, SF           |
| K318DFA-ELR  | Cruiser III, 18", FB DFA, ELR          |
| K318DFA-SF   | Cruiser III, 18", FB DFA, SF           |
| K320ADDA-ELR | Cruiser III, 20", Ht. Adj. FB DDA, ELR |
| K320ADDA-SF  | Cruiser III, 20", Ht. Adj. FB DDA, SF  |
| K320ADFA-ELR | Cruiser III, 20", Ht. Adj. FB DFA, ELR |
| K320ADFA-SF  | Cruiser III, 20", Ht. Adj. FB DFA, SF  |

## PRODUCTS

## Description

|             |                               |
|-------------|-------------------------------|
| K320DDA-ELR | Cruiser III, 20", FB DDA, ELR |
| K320DDA-SF  | Cruiser III, 20", FB DDA, SF  |
| K320DFA-ELR | Cruiser III, 20", FB DFA, ELR |
| K320DFA-SF  | Cruiser III, 20", FB DFA, SF  |

## SPECIFICATIONS

## Description

|                        |                                                                                                                                                                                                                                                             |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Warranty               | Limited Lifetime                                                                                                                                                                                                                                            |
| Product Weight         | 35 lb   36 lb   38 lb                                                                                                                                                                                                                                       |
| Weight Capacity        | 300 lb   350 lb                                                                                                                                                                                                                                             |
| Height                 | 35"                                                                                                                                                                                                                                                         |
| Seat To Floor Height   | 17.5" - 19.5"                                                                                                                                                                                                                                               |
| Carton Shipping Weight | 43 lbs or less                                                                                                                                                                                                                                              |
| Back Height            | 16"                                                                                                                                                                                                                                                         |
| CA Prop 65             | [WARNING: This product can expose you to chemicals that are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> .] |

## ACCESSORIES

## Description

|            |                                          |
|------------|------------------------------------------|
| STDS860    | Forwrd Stablzrs/Univ.Fit ,1pr/bx, BX     |
| STDS4S2432 | Caster with 11mm Bearings, 1/ea, EA      |
| STDS819    | Anti Tippers,Cruiser,1pr/bx, BX          |
| STDS1034   | Wheelchair Cane/Crutch Holder,1/ea, EA   |
| STDS801    | Brake Handle Ext.,8", 1/ea, EA           |
| WASR       | Limb Support, Right,1/cs, CS             |
| STDS834    | OverheadAnti-Theft Bar,Single,1/ea, EA   |
| STDS806    | Anti-Fold/Theft Device for w/c,1/ea, BX  |
| STDS820    | Telescoping IV Pole,W/C, 1/bx, BX        |
| STDS856    | Seat Belt,60"Velcro-type,1/ea, EA        |
| STDS851    | Seat Belt, Velcro Close,1/ea, EA         |
| STDS855    | Seat Belt,60"" Auto-type,1/ea, EA        |
| STDS850    | Seat Belt, Clasp Type,1/ea, EA           |
| STDSSHK-K3 | Super Hemi Kit, Cruiser 3 & X4, 1/ea, EA |
| STDS803    | Oxygn Tank Holdr for W/C,1/cs, CS        |