

## BESTCARE BATTERY ADAPTER-FULL ELEC LIFTS

HCPCS:

| PRODUCTS       | Description                            |
|----------------|----------------------------------------|
| 1026601-GR-TN  | HandBrakeAssy,Rt,NitroTall,Blk,1/ea    |
| 1026601-G-TN   | HandBrakeAssy,Lt,NitroTall,Blk,1/ea    |
| 1026601-RNR-TN | HandBrakeAssy,Rt,NitroTall,,Red,1e     |
| 1026601-RN-TN  | HandBrakeAssy,Lt,NitroTall,Red,1e      |
| 1026601-WR-TN  | HandBrakeAssy,Rt,NitroTall,,White,1    |
| 1026601-W-TN   | HandBrakeAssy,Lt,NitroTall,,White,1e   |
| 102662-10N     | Folding Lock Mechanism, 1/pkg          |
| 102662-14G     | BackHeightAdjLatch, Gray 1/pkg         |
| 102662B-29L    | LT, Brake Assy,Blk-BL 1/ea             |
| 102662B-29R    | RT, Brake Assy,Blk-BL 1/ea             |
| 1026632-HEMIN  | Brake Cable Only, Nitro Hemi, 1/ea     |
| 1026632N       | Brake Cable Only, Nitro, 1/ea          |
| 1026632-TN     | Brake Cable & Sleeve, Nitro Tall, 1/ea |
| 102663RD-01    | Anti-tippers, 1/pr                     |
| 102663RD-02    | Anti-Tipper wheel, 1/ea                |
| 102663RD-03    | Armrest pad w/hrdwr, 1/ea              |
| 102663RD-04    | Backrest w/knobs, 1/ea                 |
| 102663RD-05    | Backrest knobs, 1/pr                   |
| 102663RD-06    | Brake Cable, 1/ea                      |
| 102663RD-07    | Brake Cable crossover box, 1/pkg       |
| 102663RD-09    | Folding Lock, 1/pkg                    |
| 102663RD-10    | Folding Strap, 1/ea                    |
| 102663RD-11    | Front Fork Cap, 1/ea                   |
| 102663RD-12    | Arm support Adj Knob, 1/ea             |
| 102663RD-13    | Arm Support Tube, 1/ea                 |
| 102663RD-14    | Hand Grip, 1/ea                        |
| 102663RD-15    | Left Hand Brake, 1/ea                  |
| 102663RD-16    | Right Hand Brake, 1/ea                 |
| 102663RD-17    | Left rear Wheel, 1/ea                  |
| 102663RD-18    | Right rear Wheel, 1/ea                 |
| 102663RD-19    | Seat Lock Assy, 1/pkg                  |
| 102663RD-20    | Left Arm Support Upright, 1/ea         |

| PRODUCTS         | Description                              |
|------------------|------------------------------------------|
| 102663RD-21      | Right Arm Support Upright, 1/ea          |
| 102663RD-22      | Seat, 1/ea                               |
| 102663RD-23      | Seat Rail SupportBracket, 1/ea           |
| 102663RD-24      | Left Slowdown Brake, 1/ea                |
| 102663RD-25      | Right Slowdown Brake, 1/ea               |
| 102663RD-26      | Stand assist Assy, 1/pkg                 |
| 102663RD-27      | Wheel Brake Blade, 1/ea                  |
| 102663RD-28      | Seat Rail Cap Assy, 1/ea                 |
| 1026645N         | Front Axle & Washer,Nitro Fork, 1/pr     |
| 10277-01N        | Front Whl w/bearings, 1/ea               |
| 10277-03GY       | Fork assy w/bearings 10277GY, 1/pkg      |
| 10277-05N        | Rear Whl w/bearings, 1/ea                |
| 10277-14N        | Seat tube caps set, 1/pkg                |
| 10277-19L        | Left Brake handle, 1/ea                  |
| 10277-20-S       | RT Hbar assy w/brake, 1/ea               |
| 10277-21-S       | LT Hbar assy w/brake, 1/ea               |
| 10277-28BR       | Brown Tote bag, 1/ea                     |
| 10278-01         | Back rest Knobs,1/pr                     |
| 10278-02         | Backrest, 1/ea                           |
| 10278-03         | Rear Wheel, 1/ea                         |
| 10278-04         | Rear Wheel Dustcap, 1/ea                 |
| 10278-05         | Rear axle, 1/pkg                         |
| 10278-06         | Wheel bearing, 1/pr                      |
| 10278-07         | Handlebar assy, LT, 1/ea                 |
| 10278-08         | Handlebar assy, RT, 1/ea                 |
| 10278-09         | Handlebar Lock assy, Lt, 1/pkg           |
| 10278-10         | Handlebar Lock assy, Rt, 1/pkg           |
| 10278-11         | Brake Cable,1/ea                         |
| 10278-12         | Brake Assy, LT, 1/pkg                    |
| 10278-13         | Brake Assy, RT, 1/pkg                    |
| 10278-14         | Front Caster, 1/ea                       |
| 10278-15         | Caster Axle assy, 1/pkg                  |
| 10278-16         | Caster Fork w/hrdwr, 1/pkg               |
| 10278-17         | Fork bearing, 1/ea                       |
| 10278-18         | Crossframe End caps, 1/pkg               |
| 10278-19         | Seat w/stays, 1/ea                       |
| 10278-20         | Tote Bag, 1/ea                           |
| 10278-21         | Cane Holder, 1/ea                        |
| 1060-656         | ExhaustMuffler Elbow (2 pack)            |
| 13244MLB         | Mast locking Bolt 1/ea                   |
| 14029M           | Mattress Only, 14029, 2-Port System, 1ea |
| 142006G-BCKL     | Matt Buckle, 14200N, 1/ea                |
| 14991C           | Polymer GelCushion Cover, 16", 1/ea      |
| 14992C           | Polymer GelCushion Cover, 18", 1/ea      |
| 14993C           | Polymer GelCushion Cover, 20", 1/ea      |
| 18081C           | Filter Cap, 18081, 5/bag                 |
| 525DD-624        | Compressor Elbow (5 pack)                |
| 5DEC041001148-CV | CABINET ASSEMBLY, 2/CV                   |
| 730-345          | STRAIGHT SPONGE HAND BLACK F.730-330,1E  |
| 791-09N          | RT, FrontWheelW/Bearings,1/ea            |
| 791-10N          | LT, FrontWheelW/Bearings,,1/ea           |

| PRODUCTS           | Description                              |
|--------------------|------------------------------------------|
| 791-22N            | Rear Wheel w/bearings, Left, 1/ea        |
| 791-32N            | Rear Wheel w/bearings, right, 1/ea       |
| 95013BR800KDVE07   | R800KDVE Rear Leg Assy GY, RT, 1/EA      |
| 95013BR800KDVE07LT | R800KDVE, LT Front Fork Assy GY, 1/ea    |
| 95013BR800KDVE07RT | R800KDVE, RT Front Fork Assy GY, 1/ea    |
| 95013BR800KDVE08   | R800KDVE Rear Leg Assy GY LT, 1/EA       |
| 95013BR800KDVE10   | R800KDVE, Front Fork Assy GY, 1/ea       |
| 9501A7953BK-2M     | FootrestAssembly,Black,7952M/20hSN#,1/ea |
| 950300099901       | Brake Cable wire w/barrel, RTL199, 1/ea  |
| 950300119901       | Loop Brake Assembly                      |
| AEROFLY-01         | Armpad, RT, 1/ea                         |
| AEROFLY-02         | Armpad, LT, 1/ea                         |
| AEROFLY-03-18      | Back Cushion,Orange, 1/ea                |
| AEROFLY-03-20      | Back Cushion,Orange, 1/ea                |
| AEROFLY-04-18      | Back Cushion,Blue, 1/ea                  |
| AEROFLY-04-20      | Back Cushion,Blue, 1/ea                  |
| AEROFLY-05-18      | Back Cushion,Red, 1/ea                   |
| AEROFLY-05-20      | Back Cushion,Red, 1/ea                   |
| AEROFLY-06-18      | Back Cushion,Grey, 1/ea                  |
| AEROFLY-06-20      | Back Cushion,Grey, 1/ea                  |
| AEROFLY-07-18      | Back Upholstery, 1/ea                    |
| AEROFLY-07-20      | Back Upholstery, 1/ea                    |
| AEROFLY-08         | Brake Cable, 1/ea                        |
| AEROFLY-09         | L/side Brake assy, 1/ea                  |
| AEROFLY-10         | R/side Brake assy, 1/ea                  |
| AEROFLY-11         | Brake Tip, 1/ea                          |
| AEROFLY-12         | Handlebar assy,L/S, 1/ea                 |
| AEROFLY-12BLK      | Handlebar assy, L/S, 1/ea                |
| AEROFLY-13         | Handlebar assy,R/S, 1/ea                 |
| AEROFLY-13BLK      | Handlebar assy, R/S, 1/ea                |
| AEROFLY-14         | Handlebar Release, 1/pkg                 |
| AEROFLY-15         | Rear Wheel, 1/ea                         |
| AEROFLY-16         | Handrim W/hrdwr, 1/ea                    |
| AEROFLY-17         | Quick Release axle, 1/ea                 |
| AEROFLY-18         | QuickRel axle sleeve, 1/pkg              |
| AEROFLY-19         | Front Caster, 1/ea                       |
| AEROFLY-20         | Front Axle, 1/pkg                        |
| AEROFLY-21         | Clothing Guard,LT, 1/ea                  |
| AEROFLY-22         | Clothing Guard,RT, 1/ea                  |
| AEROFLY-23         | Hand Brake Assy, 1/pkg                   |
| AEROFLY-24-18      | Seat Upholstery, 1/ea                    |
| AEROFLY-24-20      | Seat Upholstery, 1/ea                    |
| AEROFLY-25-18      | Seat Cushion Orange, 1/ea                |
| AEROFLY-25-20      | Seat Cushion Orange, 1/ea                |
| AEROFLY-26-18      | Seat Cushion Blue, 1/ea                  |
| AEROFLY-26-20      | Seat Cushion Blue, 1/ea                  |
| AEROFLY-27-18      | Seat Cushion Red, 1/ea                   |
| AEROFLY-27-20      | Seat Cushion Red, 1/ea                   |
| AEROFLY-28-18      | Seat Cushion Grey, 1/ea                  |
| AEROFLY-28-20      | Seat Cushion Grey, 1/ea                  |
| AEROFLY-29         | Fork Assy, 1/ea                          |

| PRODUCTS         | Description                              |
|------------------|------------------------------------------|
| AEROFLY-30       | Fork Bearing, 1/ea                       |
| AEROFLY-31       | Ftrest Attchmnt Block, 1/pkg             |
| AEROFLY-32       | R/S Footplate assy                       |
| AEROFLY-33       | L/S Footplate assy                       |
| AEROFLY-34       | Crossframe                               |
| AEROFLY-34-20    | Crossframe, 1/ea                         |
| AEROFLY-34-20BLK | 20" Crossframe, 1/ea                     |
| AEROFLY-34BLK    | Crossframe, 1/ea                         |
| AEROFLY-34N      | Crossframe, 1/ea                         |
| AEROFLY-34NBLK   | Crossframe, 1/ea                         |
| AEROFLY-35       | Crossframe guide set                     |
| AEROFLY-36       | Crossframe end cap set                   |
| AEROFLY-37       | L/S Sideframe                            |
| AEROFLY-37-20    | L/S Sideframe, 1/ea                      |
| AEROFLY-37-20BLK | 20 " L/S Sideframe, 1/ea                 |
| AEROFLY-37BLK    | L/S Sideframe, 1/ea                      |
| AEROFLY-37N      | L/S Sideframe, 1/ea                      |
| AEROFLY-37NBLK   | L/S Sideframe, 1/ea                      |
| AEROFLY-38       | R/S Sideframe                            |
| AEROFLY-38-20    | R/S Sideframe, 1/ea                      |
| AEROFLY-38-20BLK | 20" R/S Sideframe, 1/ea                  |
| AEROFLY-38BLK    | R/S Sideframe, 1/ea                      |
| AEROFLY-38N      | R/S Sideframe, 1/ea                      |
| AEROFLY-38NBLK   | R/S Sideframe, 1/ea                      |
| AEROFLY-39       | Sideframe end caps. 1/pr                 |
| AEROFLY-40       | Anti-Tipper, AeroFly, 1/pr               |
| AEROFLY-41       | Cup Holder Bracket,1/st                  |
| AEROFLY-42       | Footrests, 1/PR                          |
| BLWTRP-01        | Cotter pins w/straps, 1/pkg              |
| BLWTRP-02        | Knobs & Velcro, 1/pkg                    |
| BSB-79667        | Head Actuator, 1/EA                      |
| BSB-79670        | Foot Actuator, 1/EA                      |
| BSB-81799        | Hand Control, 1/EA                       |
| BSB-85055        | Power cord plug, 1/EA                    |
| BSB-85381-JB     | BSB JUNCTION BOX, 1/EA)                  |
| BSB-93126        | Hi/Lo Actuator, 1/EA                     |
| BSB-EC           | End Caps, 1/pkg                          |
| BSB-FK-00-004    | Finger Kit set, 1/pkg                    |
| BSB-HARDWARE     | Hardware Pack, 1/PKG                     |
| BSB-HCKEY        | Hand control lock key, 1/ea              |
| BSB-JUNIOR-MATC  | Bradshaw Jr Contour Foam Matt. CVR, 1/ea |
| BSB-LOCKBOX      | Hand Control Storage Box, 1/EA           |
| BSB-RST          | Ratchet w/hardware, 1/PKG                |
| BSB-WHEEL        | Locking Wheel w/HRDWR, 1/ea              |
| C23-00103        | Footrests Fusion Tall, Green,1/PR        |
| CFPC17FS-01      | Anti-Tipper wheel, 1/ea                  |
| CFPC17FS-02      | Back Frame with Uph, 1/ea                |
| CFPC17FS-03      | 24V/12AH, Battery, 1/ea                  |
| CFPC17FS-04      | Battery Tray w/hrdwr, 1/pkg              |
| CFPC17FS-05      | Cable Clip, 1/ea                         |
| CFPC17FS-06      | Caster axle, 1/ea                        |

| PRODUCTS           | Description                             |
|--------------------|-----------------------------------------|
| CFPC17FS-07        | Front Caster, 1/ea                      |
| CFPC17FS-08        | Controller w/hrdwr, 1/pkg               |
| CFPC17FS-09        | Dust Cap, 1/pr                          |
| CFPC17FS-10        | Folding Latch, 1/pkg                    |
| CFPC17FS-11        | Footrest Assy, 1/ea                     |
| CFPC17FS-12        | Front Fork aasy, 1/pkg                  |
| CFPC17FS-13        | Hub Cap, 1/pr                           |
| CFPC17FS-14        | Joystick, 1/ea                          |
| CFPC17FS-15        | Joystick Hardware, 1/pr                 |
| CFPC17FS-16        | Joystick Mount Assy, 1/pkg              |
| CFPC17FS-17        | Left Armrest Assy, 1/pkg                |
| CFPC17FS-18        | Right Armrest Assy, 1/pkg               |
| CFPC17FS-19        | Left Motor w/hrdwr, 1/pkg               |
| CFPC17FS-20        | Right Motor w/hrdwr, 1/pkg              |
| CFPC17FS-21L       | Rear Wheel, Left, 1/ea                  |
| CFPC17FS-21R       | Rear Wheel, Right 1/ea                  |
| CFPC17FS-22        | Seat Cushion, 1/ea                      |
| CFPC17FS-23        | Seat Uph, w/hrdwr, 1/ea                 |
| CFPC17FS-24        | Seat Uph screws, 8/pkg                  |
| CFPC17FS-25        | Wire Harness, 1/ea                      |
| CFPC17FS-26        | Cup Holder w/Brkt, 1/pkg                |
| CFPC17FS-27        | Cap Nut, 8/pkg                          |
| CFPC17FS-28        | Nylon inserts, 1/pr                     |
| CLN400-20-26N      | Leg lifting piston 100N, 1/ea           |
| CLN400-20-28N      | Dual Leg lifting lever cable assy, 1/ea |
| CSS-R2452          | Spica Shldr-crotch pad set, 1/pkg       |
| DQ8432-INTENSITYKN | INTENSITY KNOB-QUATTRO 2.5 & COMBO CARE |
| DRI-1675+H         | Three position Wand Valve, 1/ea         |
| DRI-PRDS1650       | Quick Connect for Valve, 1/ea           |
| FG-1100            | USB Cable Assembly,w/magnet 1/ea        |
| FG-1101            | Hand Controller, 1/ea                   |
| FG-1102            | Straps, Long-Short, 1/pkg               |
| FG-1105            | USB wall adapter, 1/ea                  |
| FG-1106            | NexStride Main Unit, 1/ea               |
| KA 1057            | Knob & washer, KA 1050, 1pr/ea          |
| LRA402225-02       | Rear Mirror - Right                     |
| MD10300-01         | Underarm Pad, 1/pr                      |
| MD10300-02         | Bolt,WingNut,Crutch Handle,1/pr         |
| MD30100-01         | Seat, 1/ea                              |
| MD30100-02         | Frame Lock Block,1/ea                   |
| MD30100-03         | Arm pad w/hardware, 1/ea                |
| MD30100-04         | Rear legsw/glides, 1/pr                 |
| MD30100-04BK       | Rear legs w/glides, 1/pr                |
| MD30100-05         | Walker Wheels, 5",1/pr                  |
| MD30100-05BK       | Walker Wheels, 5",1/pr                  |
| MD50100-02         | Leg Tip, 4/pkg                          |
| MD50100-03         | Hardware pack, 1/pr                     |
| MD50100-04GR       | Back support, GR, 1/ea                  |
| MD50100-04TP       | Back support, tp, 1/ea                  |
| MD50100-04WH       | Back support, wh, 1/ea                  |
| MD50100-05L-GR     | Left Side Arm, 1/ea                     |

| PRODUCTS       | Description                           |
|----------------|---------------------------------------|
| MD50100-05L-TP | Left Side Arm, 1/ea                   |
| MD50100-05L-WH | Left Side Arm, 1/ea                   |
| MD50100-05R-GR | Right Side Arm, 1/ea                  |
| MD50100-05R-TP | Right Side Arm, 1/ea                  |
| MD50100-05R-WH | Right Side Arm, 1/ea                  |
| MD50100-06L    | Left Side Back Support, 1/ea          |
| MD50100-06R    | Right Side Back Support, 1/ea         |
| MD50100GR-01   | Bath Seat, GR, 1/ea                   |
| MD50100GR-02   | GR Leg Tip, 4/pkg                     |
| MD50100TP-01   | Bath Seat, TP, 1/ea                   |
| MD50100TP-02   | TP Leg Tip, 4/pkg                     |
| MD50100WH-01   | Bath Seat, WH, 1/ea                   |
| MD50100WH-02   | WH Leg Tip, 4/pkg                     |
| MD50200-02     | Backrest tube, 1/ea                   |
| MD50200-05     | Leg Frame, 1/ea                       |
| MD50200-07     | Knob set, 4/pk                        |
| MD50200-08     | Roller pin assy, 4/pk                 |
| MD50200-10     | Slide latch assy, 1/pkg               |
| MD50200-11     | Swivel latch assy, 1/pkg              |
| MD50200GR-01   | Backrest, GR, 1/ea                    |
| MD50200GR-03   | LT Armrest, 1/ea                      |
| MD50200GR-04   | RT Armrest, 1/ea                      |
| MD50200GR-06   | Leg Set, GR, 4/pk                     |
| MD50200GR-09   | Seat, GR, 1/ea                        |
| MD50200GR-12   | Leg Tip Set, GR, 4/pk                 |
| MD50200WH-01   | Backrest, WH, 1/ea                    |
| MD50200WH-03   | LT Armrest, 1/ea                      |
| MD50200WH-04   | RT Armrest, 1/ea                      |
| MD50200WH-06   | Leg Set, WH, 4/pk                     |
| MD50200WH-09   | Seat, WH, 1/ea                        |
| MD50200WH-12   | Leg Tip Set, WH, 4/pk                 |
| MD770525-L     | MD770525 Leg, 1/ea                    |
| MD770525-T     | MD770525 Tip, 1/ea                    |
| MD770535-L     | MD770535 Leg, 1/ea                    |
| MD770535-T     | MD770535 Tips, 4/pkg                  |
| MD785340-01    | Tub Rail Adj Knob, 1/ea               |
| NOW1D-CH       | New Oslo Wardrobe Door, Cherry, 1/ea  |
| NOW1D-FM       | New Oslo Wardrobe Door, FM, 1/ea      |
| NOW1D-OAK      | New Oslo Wardrobe Door, Oak, 1/ea     |
| NOW1H          | Hinge for Oslo Wardrobe, 1/ea         |
| NOW1HT         | Hanger tube, 1/ea                     |
| NOW1Z-CH       | New Oslo Toe kick, 1/ea               |
| NOW1Z-FM       | New Oslo Toe kick, 1/ea               |
| NOW1Z-OAK      | New Oslo Toe kick, 1/ea               |
| NRS18010-35    | Hardware pack, 1/pkg                  |
| NRS185006-08BA | CasterWithLeg- NRS Series - AST, 1/ea |
| NWCRUISER-01   | Anti-Tipper, 1/pr                     |
| NWCRUISER-02   | Full armpad assy, 1/ea                |
| NWCRUISER-03   | Armrest Guide, 1/ea                   |
| NWCRUISER-04   | Lt Armrest assy, 1/ea                 |
| NWCRUISER-05   | Rt Armrest Assy, 1/ea                 |

| PRODUCTS       | Description                        |
|----------------|------------------------------------|
| NWCRUISER-06   | Armrest Lock, 1/ea                 |
| NWCRUISER-07   | Armrest Pivot, 1/ea                |
| NWCRUISER-08   | Rear axle sleeve, 1/ea             |
| NWCRUISER-09L  | LT Back Cane Support, 1/ea         |
| NWCRUISER-09R  | RT Back Cane Support, 1/ea         |
| NWCRUISER-10   | Folding Cane Hinge, 1/pkg          |
| NWCRUISER11-16 | 16" Back Cushion, 1/ea             |
| NWCRUISER11-18 | 18" Back Cushion, 1/ea             |
| NWCRUISER11-20 | 20" Back Cushion, 1/ea             |
| NWCRUISER12-16 | 16" Back upholstery, 1/ea          |
| NWCRUISER12-18 | 18" Back upholstery, 1/ea          |
| NWCRUISER12-20 | 20" Back upholstery, 1/ea          |
| NWCRUISER13-16 | 16" seat upholstery, 1/ea          |
| NWCRUISER13-18 | 18" seat upholstery, 1/ea          |
| NWCRUISER13-20 | 20" seat upholstery, 1/ea          |
| NWCRUISER-14   | LT. Seat saddle armrest rcvr, 1/ea |
| NWCRUISER-15   | RT. Seat saddle armrest rcvr, 1/ea |
| NWCRUISER-16   | LT, Clothing Guard, 1/ea           |
| NWCRUISER-17   | RT, Clothing Guard, 1/ea           |
| NWCRUISER-18   | Rear wheel assy w/handrim, 1/ea    |
| NWCRUISER-19   | Handrim, w/hardware, 1/ea          |
| NWCRUISER-20   | Quick Release axle, 1/ea           |
| NWCRUISER-21   | Rear wheel bearing, 1/ea           |
| NWCRUISER-22   | Caster axlew/spacers, 1/pkg        |
| NWCRUISER-23   | Front Fork assy, 1/pkg             |
| NWCRUISER-24   | Caster, 1/ea                       |
| NWCRUISER-25   | Lt side Frame, 1/ea                |
| NWCRUISER-26   | Rt side Frame, 1/ea                |
| NWCRUISER-27   | Lt side Frame, 1/ea                |
| NWCRUISER-28   | Rt side Frame, 1/ea                |
| NWCRUISER-29L  | LT side Brake assy, 1/ea           |
| NWCRUISER-29R  | RT side Brake assy, 1/ea           |
| NWCRUISER-30   | Brake tip, 1/ea                    |
| NWCRUISER-31   | NWC 16 Footrest, 1/pr              |
| NWCRUISER-32   | Heel Loop assy, 1/ea               |
| NWCRUISER-33   | Footrest Block, 1/pkg              |
| NWCRUISER-34   | X-Frame End cap set, 1/pkg         |
| NWCRUISER35-16 | Crossframe, 1/ea                   |
| NWCRUISER35-18 | Crossframe, 1/ea                   |
| NWCRUISER35-20 | Crossframe, 1/ea                   |
| NWCRUISER36    | Toolkit, 1/ea                      |
| NWCRUISER37    | NWC 1820 Footrest, 1/pr            |
| OT 4BT-L       | BackTrigger,Lft,OT4000,1/ea        |
| OT 4BT-R       | Back Trigger,Rght, OT4000,1/ea     |
| OT 4ST-L       | SeatTrigger,Lft,OT4000,1/ea        |
| OT 4ST-R       | Seat Trigger, Rght,OT4000,1/ea     |
| PB411LEGS      | BSB31C, PB411 Legs 1EA/            |
| PRT-CPR-4800   | RIBBON CPR 4800                    |
| RTL12301DK-LEG | Leg assy, 1/ea                     |
| RTL12301LT-LEG | Leg assy, 1/ea                     |
| SIM02-0229008  | 8 CELL Single Battery, 1/EA        |

| PRODUCTS           | Description                              |
|--------------------|------------------------------------------|
| SIM02-0229008-16   | 16 CELL Double Battery, 1/EA             |
| SIM02-0229010      | Partical Filter, 1/PR                    |
| SIM02-0229011      | Inlet Filter, 1/PR                       |
| SIM02-0229013      | AC Adapter, 1/EA                         |
| SIM02-0229014      | AC Power Cord, 1/EA                      |
| SIM02-0229015      | DC Adapter, 1/EA                         |
| SIM02-0229017      | Compressor, 1/ea                         |
| SIM02-0229018      | Main Conrol Board, 1/ea                  |
| SIM02-0229019      | Display Board, 1/ea                      |
| SIM02-0229020      | 3-Way Valve Module, 1/ea                 |
| SIM02-0229021      | 2-Way Valve Module, 1/ea                 |
| SIM02-0229022      | External Battery Charger, 1/EA           |
| SIM02-0229023      | Cabinet Housing, 1/ea                    |
| SIM02-0229024      | Cooling Fan, 1/ea                        |
| SIM02-0229090      | Sieve Bed, 1/EA                          |
| SIM02-0238009      | Carry Bag, 1/EA                          |
| SIM02-SIEVETOOL    | Ssimo2 Sievebed tool, 4/pkg              |
| SL182A21N          | Support Bar Hrdwre,Bolts, 1/PR           |
| SP01-903-10019EAIW | HeadWidthExtension,Right,P903W, 1/ea     |
| SP01-903-10020EAIW | HeadWidthExtension,Left,P903W, 1/ea      |
| SP01-903W-10016-20 | P903W Foot actuator hardware, 1/pkg      |
| SP01-ANGLE -RW     | LTC Bed Angle Ind. 903W RT, assy, 1/pkg  |
| SP01-ANGLE-L       | LTC Bed Angle Ind. LT, assy, 1/pkg       |
| SP01-ANGLE-LW      | LTC Bed Angle Ind, 903W. LT, assy, 1/pkg |
| SP01-ANGLE-R       | LTC Bed Angle Ind. RT, assy, 1/pkg       |
| SP01-P703-10009AE  | FtBrdAdjLgthMntBrcktW/Hrdw,P703,1/ea     |
| SP01-P703WE-1EAI   | Head Width Extension, Right, P703, 1/ea  |
| SP01-P703WE-2EAI   | Head Width Extension, Left, P703, 1/ea   |
| SP01-P750-10019EAI | HeadWidthExtension,Right,P903/P750,1/ea  |
| SP01-P750-10020EAI | HeadWidthExtension,Left,P903/P750,1/ea   |
| SP01-P903W-05AE    | HdBrdMountBracketsW/Hrdw, P903W, 1/pr    |
| SP01-P903W-08AE    | FtBrdMountBracktsW/Hrdw, P903W, 1/pr     |
| SP01-P903W-10003E  | FootDckTrckAssbly,Left, P903W, 1/ea      |
| SP01-P903W-10004E  | FootDckTrckAssbly,Right, P903W, 1/ea     |
| SP01-P903W-10005E  | BrakeLockingPedalAssembly, P903W, 1/ea   |
| SP01-P903W-10011E  | Width Mattress Retainers, P903W, 4/pkg   |
| SP01-P903W-10012E  | Length Mattress Retainers, P903W, 1/pr   |
| SP01-P903W-10016E  | Foot Bracket &Hardware, P903W,1/pkg      |
| SP01-P903W-10019E  | HeadWidthExtension,Right,P903W,1/ea      |
| SP01-P903W-10020E  | HeadWidthExtension,Left,P903W,1/ea       |
| SP01-P903W-10021E  | FootWidthExtension,Left,P903W,1/ea       |
| SP01-P903W-10022E  | FootWidthExtension,Right,P903W,1/ea      |
| SP01-P903W-10023E  | ThighWidthExtension,Left,P903W,1/ea      |
| SP01-P903W-10024E  | ThighWidthExtension,Right,P903W,1/ea     |
| SP01-P903W-13AE    | Wall Bumper, P903W, 1/ea                 |
| SP01-P903W-14AE    | CasterBrakeAssbly,FootEnd, P903W, 1/ea   |
| SP01-P903W-15AE    | HeadDeckTruckAssbly,Right, P903W, 1/ea   |
| SP01-P903W-16AE    | HeadDckTruckAssmbly,Left, P903W, 1/ea    |
| SP01-PCB300-01-58E | HeadTrckAssbly,Left,Gray,PCB 301/601/503 |
| STDS29S3140N       | Seat Rail Brckt,Lt.Frnt,Plstk.1/ea       |
| STDS29S3141N       | Seat Rail Brckt,Rt.Frnt,Plstk.1/ea       |



| PRODUCTS       | Description                             |
|----------------|-----------------------------------------|
| STDS29SK5-27SE | CrossFrame w/seat ext,Lynx,16",1ea      |
| STDS29SK5-28SE | CrossFrame w/seat ext,Lynx,18",1ea      |
| STDS29SK5-29SE | CrossFrame w/seat ext,Lynx,20",1ea      |
| STDS29SK5-44   | SeatExtensionTubes, Lynx,1/pr           |
| STDS5D470LF    | Full Arm,Left, 5D, SS Recliner,1ea      |
| STDS5D470RF    | Full Arm,Right, 5D, SS Recliner,1ea     |
| STS450-N-HC-01 | STSP450 hardware pack, 1/pkg            |
| TITANMID-07    | SideFrameAssbly,Left,TitanMidWheel, 1/e |