

## Non-Tilt Automatic Overbed Table H

HCPCS:



FIGURE A



- Spring loaded lift mechanism height adjustment from 30" 45"
- ¾" x 18" x 32" high pressure laminate top with T- molding
- 2" casters for easy maneuvering
- Column can be mounted on left or right side
- Available with "H" (Figure A) or "U" base in chrome or opal powder coat
- Optional dual mirror vanity drawer
- Base and columns available in additional powder coat finishes
- Available on drop ship basis only

| PRODUCTS    | Description                        |
|-------------|------------------------------------|
| 16009-HCBO  | OBT-Auto-LrgTp-BO-H-Chrm-SpclOrdr  |
| 16009-HCBOV | OBT-Auto-LrgTp-BO-H-Ch-Van-SpOr    |
| 16009-HCDM  | OBT-Auto-LrgTp-DM-H-Chrm-SpclOrdr  |
| 16009-HCDMV | OBT-Auto-LrgTp-DM-H-Ch-Van-SpOr    |
| 16009-HCEO  | OBT-Auto-LrgTp-EO-H-Chrm-SpclOrdr  |
| 16009-HCEOV | OBT-Auto-LrgTp-EO-H-Ch-Van-SpOr    |
| 16009-HCFM  | OBT-Auto-LrgTp-FM-H-Chrm-SpclOrdr  |
| 16009-HCFMV | OBT-Auto-LrgTp-FM-H-Ch-Van-SpOr    |
| 16009-HCGW  | OBT-Auto-LrgTp-GW-H-Chrm           |
| 16009-HCGWV | OBT-Auto-LrgTp-GW-H-Ch-Van-SpOr    |
| 16009-HCNT  | OBT-Auto-LrgTp-NT-H-Chrm-SpclOrdr  |
| 16009-HCNTV | OBT-Auto-LrgTp-NT-H-Ch-Van-SpOr    |
| 16009-HCQO  | OBT-Auto-LrgTpl-QO-H-Chrm-SpclOrdr |
| 16009-HCQOV | OBT-Auto-LrgTpl-QO-H-Ch-Van-SpOr   |
| 16009-HCSO  | OBT-Auto-LrgTp-SO-H-Chrm-SpclOrder |
| 16009-HCSOV | OBT-Auto-LrgTp-SO-H-Ch-Van-SpOr    |
| 16009-HCWC  | OBT-Auto-LrgTp-WC-H-Chrm-SpclOrdr  |
| 16009-HCWCV | OBT-Auto-LrgTp-WC-H-Ch-Van-SpOr    |
| 16009-HOBO  | OBT-Auto-LrgTp-BO-H-Op-SpOr        |
| 16009-HOBOV | OBT-Auto-LrgTp-BO-H-Op-Van-SpOr    |
| 16009-HODM  | OBT-Auto-LrgTp-DM-H-Op-SpOr        |
| 16009-HODMV | OBT-Auto-LrgTp-DM-H-Op-Van-SpOr    |
| 16009-HOEO  | OBT-Auto-LrgTp-EO-H-Op-SpOr        |
| 16009-HOEOV | OBT-Auto-LrgTp-EO-H-Op-Van-SpOr    |
| 16009-HOFM  | OBT-Auto-LrgTp-FM-H-Op-SpOr        |

## PRODUCTS

## Description

|             |                                  |
|-------------|----------------------------------|
| 16009-HOFMV | OBT-Auto-LrgTp-FM-H-Op-Van-SpOr  |
| 16009-HOGW  | OBT-Auto-LrgTp-GW-H-Op-SpOr      |
| 16009-HOGWV | OBT-Auto-LrgTp-GW-H-Op-Van-SpOr  |
| 16009-HONT  | OBT-Auto-LrgTp-NT-H-Op-SpOr      |
| 16009-HONTV | OBT-Auto-LrgTp-NT-H-Op-Van-SpOr  |
| 16009-HOQO  | OBT-Auto-LrgTpl-QO-H-Op-SpOr     |
| 16009-HOQOV | OBT-Auto-LrgTpl-QO-H-Op-Van-SpOr |
| 16009-HOSO  | OBT-Auto-LrgTp-SO-H-Op-SpOr      |
| 16009-HOSOV | OBT-Auto-LrgTp-SO-H-Op-Van-SpOr  |
| 16009-HOWC  | OBT-Auto-LrgTp-WC-H-Op-SpOr      |
| 16009-HOWCV | OBT-Auto-LrgTp-WC-H-Op-Van-SpOr  |