

## Non-Tilt Designer Overbed Table U

HCPCS:



- Spring loaded lift mechanism provides infinite adjustment from 28" - 45"
- MDF core with formed vinyl top
- 15" x 30" top with 1/2" bullnose edgemold provides
- a protective 1/4" lip against spills
- Twin wheel 2" casters for easy maneuvering
- Available with "H" or "U" base (Figure A) in chrome
- or opal powder coat
- Optional dual mirror vanity drawer
- Base and columns available in additional powder
- coat finishes
- Available on drop ship basis only

| PRODUCTS    | Description                      |
|-------------|----------------------------------|
| 16011-UCFM  | OBT-Designer-FM-U-Chrml-Spcl     |
| 16011-UCFMV | OBT-Designer-FM-U-Chrml-Van-Spcl |
| 16011-UCGW  | 1.4-Designer-GW-U-Chrm-Spcl      |
| 16011-UCGWV | OBT-Designer-GW-U-Chrm-Van-Spcl  |
| 16011-UCHM  | OBT-Designer-DM-U-Opal-Van-Spcl  |
| 16011-UCQO  | OBT-Designer-QO-U-Chrm-Spcl      |
| 16011-UCQOV | OBT-Designer-QO-U-Chrm-Van-Spcl  |
| 16011-UCWCV | OBT-Designer-WC-U-Chrm-Van-Spcl  |
| 16011-UOFM  | OBT-Designer-FM-U-Opal-Spcl      |
| 16011-UOFMV | OBT-Designer-FM-U-Opal-Van-Spcl  |
| 16011-UOGW  | OBT-Designer-GW-U-Opal-Spcl      |
| 16011-UOGWV | OBT-Designer-GW-U-Opal-Van-Spcl  |
| 16011-UOQO  | OBT-Designer-QO-U-Opal-Spcl      |
| 16011-UOQOV | OBT-Designer-QO-U-Opal-Van-Spcl  |
| 16011-UOWC  | OBT-Designer-WC-U-Opal-Spcl      |
| 16011-UOWCV | OBT-Designer-WC-U-Opal-Van-Spcl  |