

## Delta® Ultra- Light 1000, Semi-Electric Bed

HCPCS: E0295



FIGURE A



FIGURE B



FIGURE C



FIGURE D



FIGURE E

- The Delta 1000 is truly universal because the bed frame can be used with Drive's and most other manufacturers' bed ends, old and new
- The transition box mounted on the foot section is key to interchangeability (Figure A)
- The transition box allows you to change the rotation of the high/low shaft
- Headboard is taller than footboard to better fit home decor (Figure B)
- The wood grain panels are break and scratch resistant
- Foot section weighs 50% less than conventional foot sections to make deliveries safe and easy
- Once installed, the high/low shaft will stay with the bed to eliminate loss or forgetting on future installations (Figure C)
- Labels and color-coded springs assure accurate installation of side rails for patient safety (Figure D)
- Unique motor is completely self-contained to reduce weight and noise
- The motor assembly can be installed and removed with patient in bed
- Bed, side rails and mattress safety-tested by SGS, a nationally recognized testing facility
- Satisfies all applicable FDA entrapment guidelines
- The motor is UL approved
- In the event of a power failure, a 9 volt battery, located in the motor, can lower the head and foot sections nine times
- No crank needed
- New and improved hand pendant has large, easy-to-use controls (Figure E)
- Bed ships in two cartons
- Channel frame construction provides superior strength and reduced weight
- Zinc-coated spring deck
- Extension kit available (model #15030EXTKIT) extends length from 80" to 84"
- Patent Pending
- Weight Capacity 450 lbs

### PRODUCTS

### Description

| PRODUCTS        | Description                           |
|-----------------|---------------------------------------|
| 15030           | SemiElectricUltraLtBed,1/cs           |
| 15030BV-FR      | UltraLt.PlusSemiElecBedw/FullR        |
| 15030BV-HR      | UltraLt. PlusSemiElecBedw/Half        |
| 15030BV-PKG     | UltraLt.PlusSemi.Elec.BedPkg,1        |
| 15030BV-PKG-1   | Ultra Lt.Semi-ElecBed Pkgw/Half       |
| 15030BV-PKG-11  | Delta Semi,FullRail,QuickEasyFoam,1ea |
| 15030BV-PKG-12  | Delta Semi,HalfRail,QuickEasyFoam,1ea |
| 15030BV-PKG-1-T | Ultra Lt.Semi-ElecBed Pkgw/Half       |
| 15030BV-PKG-2   | Ultra Lt.PlusSemiElecBedPkg,1 p       |
| 15030BV-PKG-4   | Semi Electric Ultra Lt.Bed Pkg,1/cs   |
| 15030BV-PKG-T   | UltraLt.PlusSemi.Elec.BedPkg,1        |

**SPECIFICATIONS****Description**

|                        |   |
|------------------------|---|
| Warranty               | (Original Purchaser) 5 Years on Motor and Hand Control, Limited Lifetime on Welds and Frame, 1 Year on All Other Parts and Components |
| Weight Capacity        | 450 lbs maximum weight limit includes weight of occupant  |
| Carton Shipping Weight | 179 lb  |
| Weight                 | 163 lb  |

**ACCESSORIES****Description**

|          |                                       |
|----------|---------------------------------------|
| 15030HBC | Bedding in a Box,1 EA,5/CS, CS        |
| 15030HBL | Hospital Bed Linen Kit,1 EA,10/CS, CS |