

Delta® Ultra- Light 1000, Semi-Electric Bed

HCPCS:



FIGURE A



FIGURE B




FIGURE C



FIGURE D



FIGURE E

- The Delta 1000 is truly universal because the bed frame can be used with Drive's and most other manufacturers' bed ends, old and new
- The transition box mounted on the foot section is key to interchangeability (Figure A)
- The transition box allows you to change the rotation of the high/low shaft
- Headboard is taller than footboard to better fit home decor (Figure B)
- The wood grain panels are break and scratch resistant
- Foot section weighs 50% less than conventional foot sections to make deliveries safe and easy
- Once installed, the high/low shaft will stay with the bed to eliminate loss or forgetting on future installations (Figure C)
- Labels and color-coded springs assure accurate installation of side rails for patient safety (Figure D)
- Unique motor is completely self-contained to reduce weight and noise
- The motor assembly can be installed and removed with patient in bed
- Bed, side rails and mattress safety-tested by SGS, a nationally recognized testing facility
- Satisfies all applicable FDA entrapment guidelines
- The motor is UL approved
- In the event of a power failure, a 9 volt battery, located in the motor, can lower the head and foot sections nine times
- No crank needed
- New and improved hand pendant has large, easy-to-use controls (Figure E)
- Bed ships in two cartons
- Channel frame construction provides superior strength and reduced weight
- Zinc-coated spring deck
- Extension kit available (model #15030EXTKIT) extends length from 80" to 84"
- Patent Pending
- Weight Capacity 450 lbs

PRODUCTS	Description
15030	SemiElectricUltraLtBed,1/cs
15030BV-FR	UltraLt.PlusSemiElecBedw/FullR
15030BV-HR	UltraLt. PlusSemiElecBedw/Half
15030BV-PKG	UltraLt.PlusSemi.Elec.BedPkg,1
15030BV-PKG-1	Ultra Lt.Semi-ElecBed Pkgw/Half
15030BV-PKG-11	Delta Semi,FullRail,QuickEasyFoam,1ea
15030BV-PKG-12	Delta Semi,HalfRail,QuickEasyFoam,1ea
15030BV-PKG-1-T	Ultra Lt.Semi-ElecBed Pkgw/Half
15030BV-PKG-2	Ultra Lt.PlusSemiElecBedPkg,1p
15030BV-PKG-4	Semi Electric Ultra Lt.Bed Pkg,1/cs
15030BV-PKG-T	UltraLt.PlusSemi.Elec.BedPkg,1

SPECIFICATIONS	Description
Warranty	(Original Purchaser) 5 Years on Motor and Hand Control, Limited Lifetime on Welds and Frame, 1 Year on All Other Parts and Components
Weight Capacity	450 lbs maximum weight limit includes weight of occupant
Carton Shipping Weight	179 lb
Weight	163 lb
ACCESSORIES	Description
15030HBC	Bedding in a Box,1 EA,5/CS, CS
15030HBL	Hospital Bed Linen Kit,1 EA,10/CS, CS