

## Non-Tilt Designer Overbed Table H

HCPCS:



- Spring loaded lift mechanism provides infinite adjustment from 28" - 45"
- MDF core with formed vinyl top
- 1.5" x 30" top with ½" bullnose edgemold provides
- a protective ¼" lip against spills
- Twin wheel 2" casters for easy maneuvering
- Available with "H" or "U" base (Figure A) in Chrome or Opal Powder Coat
- Optional dual mirror vanity drawer
- Available on drop ship basis only

### PRODUCTS

### Description

|             |                                 |
|-------------|---------------------------------|
| 16011-HCFM  | OBT-Designer-FM-H-Chrm-SpclOrd  |
| 16011-HCFMV | OBT-Designer-FM-H-Chrm-Van-Spcl |
| 16011-HCGN  | OBT-Designer-GN-H-Chrm-SpclOrd  |
| 16011-HCGW  | OBT-Designer-GW-H-Chrm-SpclOrd  |
| 16011-HCGWV | OBT-Designer-GW-H-Chrm-Van-Spcl |
| 16011-HCHM  | OBT-Designer-HM-H-Chrm-SpclOrd  |
| 16011-HCQO  | OBT-Designer-QO-H-Chrm-SpclOrd  |
| 16011-HCQOV | OBT-Designer-QO-H-Chrm-Van-Spcl |
| 16011-HCWC  | OBT-Designer-WC-H-Chrm-SpclOrd  |
| 16011-HCWCV | OBT-Designer-WC-H-Chrm-Van-Spcl |
| 16011-HOFM  | OBT-Designer-FM-H-Opal-Spcl     |
| 16011-HOFMV | OBT-Designer-FM-H-Opal-Van-Spcl |
| 16011-HOGW  | OBT-Designer-GW-H-Opal          |
| 16011-HOGWV | OBT-Designer-GW-H-Opal-Van      |
| 16011-HOQO  | OBT-Designer-QO-H-Opal-Spcl     |
| 16011-HOQOV | OBT-Designer-QO-H-Opal-Van-Spcl |
| 16011-HOWC  | OBT-Designer-WC-H-Opal-Spcl     |
| 16011-HOWCV | OBT-Designer-WC-H-Opal-Van-Spcl |

### SPECIFICATIONS

### Description

|                        |                  |
|------------------------|------------------|
| Warranty               | Limited Lifetime |
| Height                 | 28" - 45"        |
| Base Dimensions        | 15" x 28"        |
| Carton Shipping Weight | 28 lb            |
| Weight                 | 25 lb            |