

Non-Tilt Premium Multi-Feature Overbed Table

U

HCPCS:



- Pneumatic cylinder lift mechanism provides infinite adjustment from 27" 42"
- High pressure laminate top with raised urethane lip for spill containment
- Dual removable cup holders with flexible grip tabs
- Storage between cup holders perfect for pens, cell phones, etc
- Dual hand grips and 2" casters for easy maneuvering
- Column can be mounted on left or right side
- Available with "H" or "U" base in chrome or opal powder coat
- Optional dual mirror vanity drawer
- Base and columns available in additional powder coat finishes
- Available on drop ship basis only

| PRODUCTS    | Description                      |
|-------------|----------------------------------|
| 16005-UCBO  | OBT-Prem-BO-U-Chrm-SpclOrdr      |
| 16005-UCBOV | OBT-Prem-BO-U-Chrm-Van-SpclOrdr  |
| 16005-UCDM  | OBT-Prem-FM-U-Chrm-SpclOrdr      |
| 16005-UCDMV | OBT-Prem-FM-U-Chrm-Van-SpclOrdr  |
| 16005-UCEO  | OBT-Prem-EO-U-Chrm-SpclOrdr      |
| 16005-UCEOV | OBT-Prem-EO-U-Chrm-Van-SpclOrdr  |
| 16005-UCFM  | OBT-Prem-FM-U-Chrm-SpclOrdr      |
| 16005-UCFMV | OBT-Prem-FM-U-Chrm-Van-SpclOrdr  |
| 16005-UCGW  | OBT-Prem-GW-U-Chrm-SpclOrdr      |
| 16005-UCGWV | OBT-Prem-GW-U-Chrm-Van-SpclOrdr  |
| 16005-UCNT  | OBT-Prem-NT-U-Chrm-SpclOrdr      |
| 16005-UCNTV | OBT-Prem-NT-U-Chrm-Van-SpclOrdr  |
| 16005-UCQO  | OBT-Prem-QO-U-Chrm-SpclOrdr      |
| 16005-UCQOV | OBT-Prem-QO-U-Chrm-Van-SpclOrdr  |
| 16005-UCSO  | OBT-Prem-SO-U-Chrm-SpclOrder     |
| 16005-UCSOV | OBT-Prem-SO-U-Chrm-Van-SpclOrder |
| 16005-UCWC  | OBT-Prem-WC-U-Chrm-SpclOrdr      |
| 16005-UCWCV | OBT-Prem-WC-U-Chrm-Van-SpclOrdr  |
| 16005-UOBO  | OBT-Prem-BO-U-Opal-SpclOrdr      |
| 16005-UOBOV | OBT-Prem-BO-U-Opal-Van-SpclOrdr  |
| 16005-UODM  | OBT-Prem-FM-U-Opal-SpclOrdr      |
| 16005-UODMV | OBT-Prem-FM-U-Opal-Van-SpclOrdr  |
| 16005-UOEO  | OBT-Prem-EO-U-Opal-SpclOrdr      |

| PRODUCTS    | Description                      |
|-------------|----------------------------------|
| 16005-UOEOV | OBT-Prem-EO-U-Opal-Van-SpclOrd   |
| 16005-UOFM  | OBT-Prem-FM-U-Opal-SpclOrd       |
| 16005-UOFMV | OBT-Prem-FM-U-Opal-Van-SpclOrd   |
| 16005-UOGW  | OBT-Prem-GW-U-Opal-SpclOrd       |
| 16005-UOGWV | OBT-Prem-GW-U-Opal-Van-SpclOrd   |
| 16005-UONT  | OBT-Prem-NT-U-Opal-SpclOrd       |
| 16005-UONTV | OBT-Prem-NT-U-Opal-Van-SpclOrd   |
| 16005-UOQO  | OBT-Prem-QO-U-Opal-SpclOrd       |
| 16005-UOQOV | OBT-Prem-QO-U-Opal-Van-SpclOrd   |
| 16005-UOSO  | OBT-Prem-SO-U-Opal-SpclOrder     |
| 16005-UOSOV | OBT-Prem-SO-U-Opal-Van-SpclOrder |
| 16005-UOWC  | OBT-Prem-WC-U-Opal-SpclOrd       |
| 16005-UOWCV | OBT-Prem-WC-U-Opal-Van-SpclOrd   |

| SPECIFICATIONS         | Description      |
|------------------------|------------------|
| Warranty               | Limited Lifetime |
| Weight Capacity        | 100 lbs          |
| Height                 | 27" - 42"        |
| Base Dimensions        | 18" x 32"        |
| Carton Shipping Weight | 55 lbs.          |
| Weight                 | 51 lbs.          |