

DECO2, Drive Oxygen Concentrator, 5L

HCPCS: E1390,E1390



FIGURE A



FIGURE B

- Oxygen purity up to 96%
- Oxygen concentration and flow monitoring
- Multiple safety alarms including power fail alarm
- LED display
- Continuous duty operation

PRODUCTS	Description
5DECO2DS	DECO2, Drive O2 Concentrator, 5L
SPECIFICATIONS	Description
Weight Capacity	35 lbs. (16.1 kg)
Dimensions	13in. W x 10.2in. D x 21.3in. H (330mm W x 260mm D x 540mm H)
Flow Range	0.5 - 5.0 LPM
Noise Level	50.5 dB
Oxygen Purity	90% ± 3% at 0.5 LPM
Partical Size	93% ± 3% at 1.0 - 5.0 LPM
Power Requirments	AC120V, 60Hz