

Drive DeVilbiss 10L Oxygen Concentrator

HCPCS: E1390



FIGURE A



FIGURE B

- Built upon the reliable features of the 525 concentrator, the 1025 Oxygen Concentrator is designed to provide optimal oxygen delivery for patients with varying flow requirements
- Assembled in the USA and built in the same shell as the 5 Liter, the 10 Liter Concentrator is also compatible with cylinder transfill systems
- Sold separately, the Transfill Caddy is designed with a steel frame to simply connect the 18 x 14 inch shelf, designed to support up to 40 lbs., to the DeVilbiss 10L Concentrator
- Front view (Figure A), Rear View (Figure B)
- With a weight of 42 lbs. and an identical footprint to the 525 unit, the 1025 is substantially smaller and lighter than competitive 10 Liter concentrators
- Capable of delivering 87% to 96% of O purity from 2 to 10 LPM, the 10 Liter Concentrator is an ideal investment for your patients and business alike
- Exclusive DeVilbiss OSD® (Oxygen Sensing Device), standard on every unit, monitors the oxygen produced and ensures patient safety and reliability for longer service intervals
- Equipped with accessible patient controls, bright LEDs that can be seen from a distance, protected cannula fitting and recessed humidifier nook to prevent damage

| PRODUCTS | Description |
|-------------------|--|
| 1025DS | 10L Compact Concentrator, 110v, 1/ea |
| SPECIFICATIONS | Description |
| Delivery Rate | 2.0 to 10.0 LPM |
| Oxygen Percentage | 2-10 LPM, 87-96% |
| Power Consumption | 120VAC, 60Hz |
| Power Input | 639W (avg) |
| Warranty Limited | 3 Years |
| ACCESSORIES | Description |
| 303DZ-605 | AIR FILTER 6-PKG - DFT, PKG |
| 1025D-605 | INTAKE FILTER SSP, 1/ea, EA |
| 1025D-682 | COMPRESSOR FILTER SSP, 1/ea, EA |
| PV5LD-651 | FINAL BACTERIA FILTER - DFT, 1/EA, EA |
| 525DD-650 | Transfill Rack System, 525DS Series, 1ea, EA |
| PF1100TUB | Transfill Connection Tubing, 1/ea, EA |
| XM-1 | DISS Adapter plastic, 25/Bag, EA |
| 1025D-685 | Adapter for Humidifier Bottle, EA |
| HUM 001 | Humidifier Bottle PI 50/CS, CS |

| PARTS | Description |
|------------|--|
| 1025D-603 | DOMESTIC BASE PKG, EA |
| 525DD-636 | Plastite Screw SS Pkg, EA |
| 1025DS-616 | CAPACITOR, DS SSP, 1/ea, EA |
| 1025D-615 | COMPRESSOR BOX SSP, EA |
| 1025D-632 | COMPRESSOR PLATE SSP, EA |
| 1025D-643 | DS COMPRESSOR REBUILD KIT SSP, 1/ea, EA |
| 505DZ-634 | SILICON TUBING (2'), EA |
| 525DD-639 | DOOR INTAKE FILTER PACKAGE, EA |
| 1025D-607 | FLOW METER 10L SSP, EA |
| 525DD-611 | Front Cover Package, 1/ea, EA |
| 1025D-655 | FORMED METAL TUBE SSP, EA |
| 1025D-623 | WIRE HARNESS ASSEMBLY, DS SSP, 1/ea, EA |
| 1025D-609 | MOTOR MONT SSP, EA |
| 525DD-606 | Concentrator (5L, 10L) Outlet Port, 1/ea, EA |
| 1025D-622 | PC BOARD ASSEMBLY SSP, EA |
| 1025D-612 | PRESSURE REGULATOR, EA |
| MC29D-612 | PRESSURE REGULATOR ASSY, EA |
| 1025D-617 | PURGE HARNESSE ASSEMBLY, EA |
| 525DD-612 | Rear Cover Package - with Aux Port, 1/ea, EA |
| 515ADZ-702 | ROTARY VALVE REPLACEMENT, EA |