

Inovo Brass-Core Regulator

HCPCS:



- Can provide flow rates of 0 - 25 LPM
- 12-position flow dial (0.25, 0.50, 1.0, 2.0, 3.0, 4.0, 6.0, 8.0, 10.0, 15.0, 25.0 LPM)
- Meets ASTM-G175-13 promoted ignition tests
- Inlet pressure: 500 - 3,000 psi
- Outlet pressure: 50 psi
- Outlet Type: Barb
- Connection Type: CGA 870
- 5 years expected service live
- 2-year limited warranty
- Assembled and tested in the USA

PRODUCTS	Description
IN3625-R	BrassCore,0-25LPM,CGA870,Barb,0 PTO,1/EA
IN3625-R-1	BrassCore,0-25LPM,CGA870,Barb,1 PTO,1/EA
IN3625-R-2	BrassCore,0-25LPM,CGA870,Barb,2 PTO,1/EA
SPECIFICATIONS	Description
Warranty	2-year limited warranty
Color	Black
Flow Rate	0.25, 0.5, 1.0, 2.0, 3.0, 4.0, 6.0, 8.0, 10.0, 15.0, 25.0 LPM
Liter Flow	12 settings
Product Type	Oxygen Regulator
ACCESSORIES	Description
SEAL100	Seal Washer,Conservers/Regulators,10/pkg, PKG