

## CHAD® Regulators

HCPCS:



FIGURE A

- 20-micron, sintered-bronze inlet filter
- FDA-recommended viton and brass seal washers
- Flow rate tolerances are as follows: +/- 20% for flows greater than 1.5 LPM +/- 30% for flows 1.5 LPM or less
- Meets ASTM-G175-03 promoted ignition tests
- Inlet pressure: 500 3,000 PSI
- Outlet pressure: 50 PSI
- 100% QC tested in the USA

PRODUCTS	Description
CH4808-L-BLUE	RegCHAD,Blue, 0-8L, CGA870, Barb, 1/ea
CH4815-L-BLUE	RegCHAD,Blue, 0-15L, CGA870, Barb, 1/ea

  

SPECIFICATIONS	Description
Warranty	Limited 2 Year

  

ACCESSORIES	Description
SEAL100	Seal Washer,Conservers/Regulators,10/pkg, PKG